

SANTOPRENE[®] 103-40

SANTOPRENE®

A hard, black, versatile thermoplastic vulcanizate (TPV) in the thermoplastic elastomer (TPE) family. This material combines good physical properties and chemical resistance for use in a wide range of applications. This grade of Santoprene® TPV is shear-dependent and can be processed on conventional thermoplastics equipment for injection molding, extrusion, blow molding, thermoforming or vacuum forming. It is polyolefin based and recyclable within the manufacturing stream.

Key Features

- UL listed: file #QMFZ2.E80017, Plastics Component; file #QMFZ8.E80017, Plastics Certified For Canada -Component
- Excellent ozone resistance

Product information

TPV >TPV<		ISO 1043 ISO 11469
20.7 610 -52 41 54 61	MPa % °C %	ISO 37 ISO 527-1/-2 or ISO 37 ISO 527-1/-2 or ISO 37 ASTM D 746 ISO 48-4 / ISO 868 ISO 815 ISO 815 ISO 34-1
85 85	°C ℃	UL 746B UL 746B UL 746B UL 746B
f3 f4		UL 749 UL 2157
1.5 yes HB 1 yes PLC 3	mm class mm s	IEC 60695-11-10 IEC 60695-11-10 UL 94 IEC 60695-11-10 IEC 60695-11-10 UL 94 UL 746A UL 746A
	>TPV< 9 20.7 610 -52 41 54 61 64 85 85 85 85 85 85 85 85 85 85 85 85 85	>TPV< 9 MPa 20.7 MPa 610 % -52 °C 41 54 % 61 % 64 kN/m 85 °C 85 °C 8



SANTOPRENE® 103-40

SANTOPRENE®

Electrical properties

Relative permittivity, 60Hz Arc Resistance Performance Level Category Electric Strength, Short Time, 2mm High Amperage Arc Ignition Category, 1.5 mm	2.6 PLC 5 32 PLC 0	kV/mm	IEC 62631-2-1 UL 746B ASTM D 149 UL 746A
Physical/Other properties			
Density	950	kg/m³	ISO 1183
Injection			
Drying Temperature	82	°C	
Drying Time, Dehumidified Dryer		h	
Processing Moisture Content	≤0.08	%	
Max. regrind level	20	%	
Melt Temperature Optimum	215	°C	
Min. melt temperature	165	°C	
Max. melt temperature	265	°C	
Mold Temperature Optimum	50	°C	
Min. mould temperature	20	°C	
Max. mould temperature		°C	
Back pressure	0.517		
Ejection temperature	95	°C	
Extrusion			
Drying Temperature	82	°C	
Drying Time, Dehumidified Dryer			
Melt Temperature Range	210	°C	

Additional information

Processing Notes

Processing Notes


Desiccant drying for 3 hours at 80 °C (180 °F) is recommended. Santoprene® TPV has a wide temperature processing window from 175 to 230 °C (350 to 450 °F) and is incompatible with acetal and PVC.



SANTOPRENE[®] 103-40

SANTOPRENE®

Specific volume-temperature (pvT)



Printed: 2024-05-12

Page: 3 of 3

Revised: 2024-03-25 Source: Celanese Materials Database

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication as a promise or guarantee of specific properties of our groucts. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to he lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material inductions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed for addi

© 2024 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC. KEPITAL is a registered trademark of Korea Engineering Plastics Company, Ltd.