

SANTOPRENE[®] 8211-45

SANTOPRENE®

A soft, colorable, non-hygroscopic thermoplastic vulcanizate (TPV) in the thermoplastic elastomer (TPE) family. This material combines good physical properties and chemical resistance for use in difficult injection molding applications. This grade of Santoprene® TPV is shear-dependent and can be processed on conventional thermoplastics equipment for injection molding. It is polyolefin based and recyclable within the manufacturing stream.

Key Features

- · Non-hygroscopic product, requires little to no drying before processing.
- · Neutral, easy coloring formulation.
- · Recommended for applications requiring excellent ozone resistance.
- · Used in sealing applications.
- · Recommended for applications requiring excellent flex fatigue resistance.
- · UL listed: file #QMFZ2.E80017, Plastics Component; file #QMFZ8.E80017, Plastics Certified For Canada Component.

Product information

Resin Identification Part Marking Code	TPV >TPV<		ISO 1043 ISO 11469
Typical mechanical properties			
Tensile stress at 100% elongation, perpendicular Stress at break, perpendicular Elongation at break, perpendicular Brittleness Temperature Shore A hardness, 15s	3.6 410 -62 49	°C	ISO 37 ISO 527-1/-2 or ISO 37 ISO 527-1/-2 or ISO 37 ASTM D 746 ISO 48-4 / ISO 868
Compression set, 70°C, 24h	25	%	ISO 815
Thermal properties			
RTI, electrical, 1.5mm RTI, electrical, 3.0mm RTI, strength, 1.5mm RTI, strength, 3.0mm			UL 746B UL 746B UL 746B UL 746B
Flammability			
Burning Behav. at thickness h Thickness tested UL recognition		class mm	IEC 60695-11-10 IEC 60695-11-10 UL 94
Physical/Other properties			
Density	930	kg/m³	ISO 1183
Injection			
Processing Moisture Content Max. regrind level Melt Temperature Optimum Min. melt temperature Max. melt temperature	≤0.08 20 215 165 265	% °C °C	

Printed: 2024-05-11



SANTOPRENE® 8211-45

SANTOPRENE®

Mold Temperature Optimum	50 °C
Min. mould temperature	20 °C
Max. mould temperature	80 °C
Back pressure	0.517 MPa
Ejection temperature	84 °C


Additional information

Processing Notes

Processing Notes

Desiccant drying for 3 hours at 80° C (180° F) can be performed if desired. Santoprene® TPV has a wide temperature processing window from 175 to 230°C (350 to 450° F) and is incompatible with acetal and PVC.

Specific volume-temperature (pvT)





SANTOPRENE[®] 8211-45

SANTOPRENE®

Printed: 2024-05-11

Revised: 2024-03-25 Source: Celanese Materials Database

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and rate design of any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to helowest that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust we handling of such material to adequately trained personnel only. Please call the telephone numbers listed for add

© 2024 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC. KEPITAL is a registered trademark of Korea Engineering Plastics Company, Ltd.

Page: 3 of 3